



## 3-1/2 in. Conduit Clamp, Parallel Type

By Raco  
Catalog # 2334PC

3-1/2 in. Conduit Clamp, Parallel Type



\*Representative Image

### Features

- Three available styles, Parallel, Edge and Right Angle, to meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications
- Additional sizes available

### General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Malleable Iron
UPC	050169986189

### Dimensions

Dimensions	6.275 in x 1.84 in x 4.313 in
Height	4.313 in
Length	6.275 in
Trade Size	3-1/2 in
Weight	1.904 lb
Width	1.84 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	875

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - RACO® Conduit Clamps](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-2334PC-SPEC-EN | REV 6/2024