



# 4 in. Square Box, Welded, 2-1/8 in. Deep, Eight 1/2 in. KO's and Five TKO's, TS Bracket, Flush

By RACO  
Catalog # 235

4 in. Square Box, Welded, 2-1/8 in. Deep, Eight 1/2 in. KO's and Five TKO's, TS Bracket, Flush



## Features

- TS style bracket, flush
- Combination screw heads allow quick installation
- Welded construction
- Nine 1/2 in. knockouts and Five TKO knockouts
- UL Listed
- 30.3 cu. in. capacity
- Acceptable in 2-hour fire rated walls

## Specifications

Certified Listed	UL Listed
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

## Configuration

Knockouts	<ul style="list-style-type: none"> <li>• 1/2 in</li> <li>• 1/2 - 3/4 in Combination (TKO)</li> </ul>
Bracket Type	TS, for Metal or Wood Studs

## Dimensions

Cubic Capacity	30.3 cu.in
Depth	2.125 in

Size	4 in
Actual Depth	2.402 in
Raised Ground	No
Width	4.436 in
Weight	1.008 lb.
Height	7.01 in

## General

Wiring System	Conduit
Type	Box
Fire Resistance	Yes
Material	Steel
Drawn or Welded	Welded
UPC	050169902356

## Logistics

Packaging Type	No Packaging
Carton Quantity	25
Pallet Quantity	1100

## Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)