



4 in. Square Box, Welded, 2-1/8 in. Deep, One 1/2 and Ten 3/4 in. KO's, FM Bracket

By Raco
Catalog # 236

4 in. Square Box, Welded, 2-1/8 in. Deep, One 1/2 and Ten 3/4 in. KO's, FM Bracket



Features

- FM style bracket, flush
- Combination screw heads allow quick installation
- Welded construction
- One 1/2 in. knockout and Ten 3/4 in. knockouts
- UL Listed
- 30.3 cu. in. capacity
- Acceptable in 2-hour fire rated walls
- UPC barcoded

General

Bracket Type	FM, for Metal or Wood Studs
Catalog Number	236
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in;3/4 in
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169002360
Wiring System	Conduit

Dimensions

Actual Depth	2.425 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	7.625 in
Raised Ground	No
Weight	1.112 lb
Width	4.403 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1500

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 2](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-5](#)
[Sales Drawings - 236](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-236-SPEC-EN | REV 6/2024