



3-1/2 in. Conduit Clamp, Right Angle

By Raco
Catalog # 2364RC

3-1/2 in. Conduit Clamp, Right Angle



*Representative Image

Features

- Three available styles, Parallel, Edge and Right Angle, to meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications
- Additional sizes available

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Malleable Iron
UPC	050169986288

Dimensions

Dimensions	6.16 in x 5.6 in x 2.3 in
Height	2.3 in
Length	6.16 in
Trade Size	3-1/2 in
Weight	1.36 lb
Width	5.6 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	750

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195968-3](#)
[SDS - HCC SDS](#)
[Sell Sheets - RACO® Conduit Clamps](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand