



4 in. Square Box, Welded, 2-1/8 Deep, Nine 1/2 in. KO's & Five TKO's, BOX-LOC® Series MS Bracket, Flush

By RACO
Catalog # 238



4 in. Square Box, Welded, 2-1/8 Deep, Nine 1/2 in. KO's & Five TKO's, BOX-LOC® MS Bracket, Flush

Features

- MS style BOX-LOC® bracket, flush
- Combination screw heads allow quick installation
- Welded construction
- Nine 1/2 in. knockouts and Five TKO knockouts
- UL Listed
- 30.3 cu. in. capacity
- RACO 978
- Acceptable in 2-hour fire rated walls
- UPC barcoded

Specifications

Certified Listed	UL Listed
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)

Configuration

Knockouts	<ul style="list-style-type: none"> • 1/2 in • 1/2 - 3/4 in Combination (TKO)
Bracket Type	MS, for Metal Studs
Number of Gang(s)	2-Gang

Dimensions

Cubic Capacity	30.3 cu.in
----------------	------------

Depth	2.125 in
Size	4 in
Actual Depth	2.188 in
Raised Ground	No
Width	5.5 in
Weight	1.052 lb.
Height	4.625 in

General

Wiring System	Conduit
Series	BOX-LOC® Series
Color	Gray
Type	Box
Fire Resistance	Yes
Material	Steel
Drawn or Welded	Welded
UPC	050169002384

Logistics

Packaging Type	No Packaging
Carton Quantity	25
Pallet Quantity	1250

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)