



4 in. Square Box, Welded, 2-1/8 Deep, Nine 1/2 in. KO's & Five TKO's, BOX-LOC® MS Bracket, Flush

By Raco
Catalog # 238



4 in. Square Box, Welded, 2-1/8 Deep, Nine 1/2 in. KO's & Five TKO's, BOX-LOC® MS Bracket, Flush

Features

- MS style BOX-LOC® bracket, flush
- Combination screw heads allow quick installation
- Welded construction
- Nine 1/2 in. knockouts and Five TKO knockouts
- UL Listed
- 30.3 cu. in. capacity
- RACO 978
- Acceptable in 2-hour fire rated walls
- UPC barcoded

General

Bracket Type	MS, for Metal Studs
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in.;1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169002384
Wiring System	Conduit

Dimensions

Actual Depth	2.188 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4.625 in
Raised Ground	No
Weight	1.052 lb
Width	5.5 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1250

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-5](#)
[Certifications - UL COC - E195978- 2](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC_SDS](#)
[Sell Sheets - Box Positioning Products](#)
[Sell Sheets - BOX-LOC Metal Stud Bracketed Boxes](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-238-SPEC-EN | REV 6/2024