



2 in. Rigid/IMC or EMT Service Entrance Head

By Raco
Catalog # 2408

2 in. Rigid/IMC or EMT Service Entrance Head



*Representative Image

Features

- Lightweight aluminum body construction eases installation and provides corrosion resistance
- Plastic insulator snaps out easily for quick cable insertion
- Listed for use in wet locations
- Additional sizes available

General

Catalog Number	2408
Conduit Type	Service Entrance
Connector Type	Clamp-Type
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Aluminum
UPC	050169024089

Dimensions

Dimensions	4.375 in x 4.25 in x 5.875 in
Height	5.875 in
Insulating Hole Diameter	<ul style="list-style-type: none">• 3 Holes 1 Dia in• 2 Holes 0.750 Dia in• 1 Hole 0.531 Dia in
Length	4.375 in
Trade Size	2 in

Weight	1.082 lb
Width	4.25 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed
Industry Standard(s)	UL 514B
Nema Rating	NEMA 3R

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	300

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Certifications - UL COC - E195973- 1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Product Logo - SE CABLE](#)
- [Sales Drawings - 2408 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 2408](#)
- [Terms and Conditions - HCC Terms & Conditions](#)