



4 in. Square Box, Welded, 2-1/8 in. Deep with AC/MC/Flex Clamps, Three 1/2 in. KO's and One TKO, TS Bracket, Flush

By Raco
Catalog # 241



4 in. Square Box, Welded, 2-1/8 in. Deep with AC/MC/Flex Clamps, Three 1/2 in. KO's and One TKO, TS Bracket, Flush

Features

- Welded steel construction with "TS" side-mount bracket with gauging tabs and recessed nailing spurs
- 4 in. square x 2-1/8 in. deep
- BX clamps provided for steel & alum armored cable, MCI cable, MCI-A cable, and flexible conduit
- TKO® Knockouts allow for design and installation flexibility
- Supplied with three 1/2 in. and one 1/2-3/4 in. TKO® knockouts
- Combination Phillips/slotted screw heads
- 30.3 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	TS, for Metal or Wood Studs
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in.; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Type	Box
UPC	050169902417
Wiring System	Armored Cable/Metal Clad/MCI-A/Flex

Dimensions

Actual Depth	2.188 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	7 in
Raised Ground	No
Weight	1.08 lb
Width	4.313 in

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1375

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 241](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-241-SPEC-EN | REV 6/2024