



2-1/2 in. Rigid/IMC or EMT Service Entrance Head

By Raco
Catalog # 2410

2-1/2 in. Rigid/IMC or EMT Service Entrance Head



*Representative Image

Features

- Lightweight aluminum body construction eases installation and provides corrosion resistance
- Plastic insulator snaps out easily for quick cable insertion
- Listed for use in wet locations
- Additional sizes available

General

Catalog Number	2410
Conduit Type	Service Entrance
Connector Type	Clamp-Type
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Aluminum
UPC	050169024102

Dimensions

Dimensions	5.5 in x 6.313 in x 7 in
Height	7 in
Insulating Hole Diameter	<ul style="list-style-type: none">• 3 Holes 1.313 Dia in• 3 Holes 0.875 Dia in• 1 Hole 1 Dia in
Length	5.5 in
Trade Size	2-1/2 in
Weight	2.898 lb

Width	6.313 in
-------	----------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed
Industry Standard(s)	UL 514B
Nema Rating	NEMA 3R

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	110

Product Assets

- [Brochures - HCC Products for Solar](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Certifications - UL COC - E195973- 1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Product Logo - SE CABLE](#)
- [Sales Drawings - 2410 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 2410](#)
- [Terms and Conditions - HCC Terms & Conditions](#)