



3-1/2 in. Rigid/IMC or EMT Service Entrance Head

By Raco
Catalog # 2414

3-1/2 in. Rigid/IMC or EMT Service Entrance Head



*Representative Image

Features

- Lightweight aluminum body construction eases installation and provides corrosion resistance
- Plastic insulator snaps out easily for quick cable insertion
- Listed for use in wet locations
- Additional sizes available

General

Catalog Number	2414
Conduit Type	Service Entrance
Connector Type	Clamp-Type
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Aluminum
UPC	050169024140

Dimensions

Dimensions	6.75 in x 7.75 in x 8.625 in
Height	8.625 in
Insulating Hole Diameter	3 Holes 1.313 Dia in 4 Holes 1.125 Dia in
Length	6.75 in
Trade Size	3-1/2 in
Weight	6.434 lb
Width	7.75 in

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B
Nema Rating	NEMA 3R

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	60

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195973- 1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Product Logo - SE CABLE](#)
[Sales Drawings - 2414 Customer Drawing](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-2414-SPEC-EN | REV 6/2024