



4 in. Square Box, Welded with (2) STAB-IT® Connectors on Top, 2-1/8 in. Deep, Solid Pigtail, UBS, M Bracket

By Raco
Catalog # 244MS



4 in. Square Box, Welded with (2) STAB-IT® Connectors on Top, 2-1/8 in. Deep, 600V, 8 in. #12 Solid Copper Pigtail, UBS, M Bracket

Features

- Welded steel construction with "UBS" support with preset bend points to work with wall thickness 2-1/2 to 6 in., "M" brackets on both sides of the box, two STAB-IT® connectors
- 4 in. square x 2-1/8 in. deep
- Designed for quick installation of flex, MC, MCI, MCI-A, AC, and HCF Cable
- TKO® Knockouts allow for design and installation flexibility
- Supplied with seven 1/2 in. and four 1/2-3/4 in. TKO® knockouts
- Combination Phillips/slotted screw heads
- 30.3 cu. in. capacity
- Includes 8 in. #12 solid copper ground screw
- Acceptable for use in 2-hour fire rated walls

General

Catalog Number	244MS
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in.;1/2 - 3/4 in Combination (TKO)
Type	Box
UPC	050169992449

Dimensions

Actual Depth	2.64 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4.21 in
Weight	1.181 lb
Width	5.86 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Pallet Quantity	1375

Product Assets

- [3D Models - 244MS-3D](#)
- [Brochures - STAB-iT® Electrical Boxes](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Product Logo - STAB-IT](#)
- [Sales Drawings - 244MS Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - RACO® STAB-IT](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: STAB-IT® vs competition](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-244MS-SPEC-EN | REV 6/2024