



## 4 in. Square Box, Welded with (2) STAB-IT® Connectors on Top, 2-1/8 in. Deep, Pigtail, UBS, M Bracket, Cable Mgmt Clips

By Raco  
Catalog # 244MSCM



4 in. Square Box, Welded with (2) STAB-IT® Connectors on Top, 2-1/8 in. Deep, 600V, 8 in. #12 Solid Copper Pigtail, UBS, M Bracket, Cable Management Clips

### Features

- Designed for quick installation of flex, MC, MCI, MCI-A, AC, and HCF Cable
- Welded steel construction with "UBS" support with preset bend points to work with wall thickness 2-1/2 to 6 in., "M" brackets on both side of the box, two STAB-IT® connectors with cable management clips
- TKO® Knockouts allow for design and installation flexibility
- Supplied with seven 1/2 in. and four 1/2-3/4 in. TKO® knockouts
- Combination Phillips/slotted screw heads
- 30.3 cu. in. capacity
- Includes 8 in. #12 solid copper ground pigtail
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Type	M, for Metal or Wood Studs
Catalog Number	244MSCM
Color	Gray
Fire Resistance	Yes
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Type	Box
UPC	050169972441

### Dimensions

Actual Depth	2.64 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4.17 in
Weight	1.339 lb
Width	5.86 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Pallet Quantity	1375

### Product Assets

- [3D Models - 3D PDF](#)
- [Brochures - STAB-iT® Electrical Boxes](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Product Logo - STAB-IT](#)
- [Sales Drawings - 244MSCM Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - RACO® STAB-IT](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: STAB-IT® vs competition](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-244MSCM-SPEC-EN | REV 6/2024