



## 4 in. Square Box, Welded with (2) STAB-IT® Connectors on Top, 2-1/8 in. Deep, 600V, 8 in. #12 Solid Copper Pigtail

By Raco  
Catalog # 244S



4 in. Square Box, Welded with (2) STAB-IT® Connectors on Top,  
2-1/8 in. Deep, 600V, 8 in. #12 Solid Copper Pigtail

### Features

- Welded steel construction with two STAB-IT® connectors
- 4 in. square x 2-1/8 in. deep
- TKO® Knockouts allow for design and installation flexibility
- Supplied with seven 1/2 in. and four 1/2-3/4 in. knockouts
- Combination Phillips/slotted screw heads
- 30.3 cu. in. capacity
- Includes 8 in. #12 solid copper ground pigtail
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Type	No Bracket
Catalog Number	244S
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in.; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Type	Box
UPC	050169982440

### Dimensions

Actual Depth	2.43 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4.14 in
Raised Ground	Yes
Weight	1.035 lb
Width	4 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Pallet Quantity	1750

### Product Assets

- [3D Models - 244S-3D](#)
- [Brochures - STAB-iT® Electrical Boxes](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Product Logo - STAB-IT](#)
- [Sales Drawings - 244S Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - RACO® STAB-IT](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: STAB-IT® vs competition](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-244S-SPEC-EN | REV 6/2024