



4-11/16 in. Square Box, Drawn, 1-1/2 in. Deep, Fifteen 1/2 and Two 3/4 in. KO's

By Raco
Catalog # 245

4-11/16 in. Square Box, Drawn, 1-1/2 in. Deep, Fifteen 1/2 and Two 3/4 in. KO's



Features

- Combination screw heads provide for faster installation
- TKO knockouts allow for design and installation flexibility
- Square boxes are used where multiple conductor runs are split into two or more directions to bring power to a number of electrical devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- 29.5 cu. in. capacity

General

Bracket Type	No Bracket
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169002452
Wiring System	Conduit

Dimensions

Actual Depth	2.188 in
Cubic Capacity	29.5 cu.in
Depth	1.5 in
Height	4.688 in
Raised Ground	No
Weight	0.804 lb
Width	4.688 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1650

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-245-SPEC-EN | REV 6/2024