



1/2 in. Service Entrance Liquidtight UF Connector

By Raco
Catalog # 2462



1/2 in. Service Entrance Liquidtight UF Connector

Features

- Rugged metallic construction will last the life of the installation.
- Zinc electro plated for corrosion resistance
- Steel construction
- 1/2 in. trade size
- UF wire size: 2 #14 - 2 #12

General

Accessory Type	Fitting
Conduit Type	Service Entrance
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Grommet Opening Maximum	.425 in
Grommet Opening Minimum	.225 in
Material	Steel
UPC	050169024621

Dimensions

Dimensions	0.75 in x 1.25 in x 1.25 in
Height	1.25 in
Length	0.75 in
Trade Size	1/2 in
Weight	0.166 lb
Width	1.25 in

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	100
Minimum Pack Quantity	25
Pallet Quantity	9600

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - SE CABLE](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2462-SPEC-EN | REV 6/2024