



4 in. Square Box, Welded with (2) STAB-IT® Connectors, 2-1/8 in. Deep, 600V, 8 in. #12 Solid Copper Pigtail

By Raco
Catalog # 248S



4 in. Square Box, Welded with (2) STAB-IT® Connectors, 2-1/8 in. Deep, 600V, 8 in. #12 Solid Copper Pigtail

Features

- Welded steel construction
- 4 in. square x 2-1/8 in. deep
- Designed for quick installation of flex, MC, MCI, MCI-A, AC, and HCF Cable
- TKO® Knockouts allow for design and installation flexibility
- Supplied with five 1/2 in. and three 1/2-3/4 in. TKO® knockouts
- Phillips/slotted screw heads
- 30.3 cu. in. capacity
- Pre-installed 8 in. solid #12 pigtail for faster installation
- Acceptable for use in 2-hour fire rated walls

General

Application	RACO® STAB-IT boxes are great for any job where flexible armored cable is being used RACO® Boxes are installed in walls or ceilings for lighting fixtures, switches or receptacles
Catalog Number	248S
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in.; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169500712

Dimensions

Actual Depth	2.39 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4.14 in
Raised Ground	No
Weight	1.027 lb
Width	4 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Pallet Quantity	1750

Product Assets

[3D Models - 248S-CN3D](#)
[Brochures - STAB-iT® Electrical Boxes](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Product Logo - STAB-IT](#)
[Sales Drawings - 248S-CHINA Customer Drawing](#)
[SDS - HCC SDS](#)
[Sell Sheets - RACO® STAB-IT](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: STAB-IT® with Cable Management](#)
[Video - RACO: STAB-IT® vs competition](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-248S-SPEC-EN | REV 6/2024