



1.25 in to 2 in Ground Clamp, for Bare Ground Wires, Bronze Alloy

By Raco
Catalog # 2505

1.25 in to 2 in Ground Clamp, for Bare Ground Wires, Bronze Alloy

Features

- Bronze cast construction assures ground path continuity and provides corrosion resistance
- Additional sizes available

Application

For use with grounding wire or conduit to water pipes or ground rods

General

Catalog Number	2505
Material	Bronze Alloy
UPC	050169025055

Dimensions

Dimensions	0.938 in x 3.563 in x 3.125 in
Height	3.125 in
Length	0.938 in
Weight	0.403 lb
Width	3.563 in

Conductor Related



*Representative Image

Conductor Range #2 AWG to #10AWG

Certifications And Compliance

Certified Listed UL Listed
Industry Standard(s) UL 514B

Logistics

Carton Quantity 25
Minimum Pack Quantity 25
Pallet Quantity 4375

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Certifications - UL COC-E195975-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Customer Notices - Prop 65 Notice](#)
[SDS - HCC SDS](#)
[Sell Sheets - Intersystem Bonding Bridge](#)
[Specifications - 2505](#)
[Terms and Conditions - HCC Terms & Conditions](#)