



## 0.5 in to 1 in Ground Clamp for 0.5 in Rigid Conduit, Bronze Alloy

By Raco  
Catalog # 2512

0.5 in to 1 in Ground Clamp for 0.5 in Rigid Conduit, Bronze Alloy



\*Representative Image

### Features

- Bronze cast construction assures ground path continuity and provides corrosion resistance
- Additional sizes available

### General

Application	For use with grounding wire or conduit to water pipes or ground rods
Material	Bronze Alloy
UPC	050169025123

### Dimensions

Dimensions	2.5 in x 2.25 in x 3.125 in
Height	3.125 in
Length	2.5 in
Weight	0.388 lb
Width	2.25 in

### Conductor Related

Conductor Range	#6 AWG to #10 AWG
-----------------	-------------------

### Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	6075

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC-E195975-1](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - Intersystem Bonding Bridge](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-2512-SPEC-EN | REV 6/2024