



0.5 in to 1 in Ground Clamp for 0.5 in Rigid Conduit, Bronze Alloy

By Raco
Catalog # 2512

0.5 in to 1 in Ground Clamp for 0.5 in Rigid Conduit, Bronze Alloy

Features

- Bronze cast construction assures ground path continuity and provides corrosion resistance
- Additional sizes available

Application

For use with grounding wire or conduit to water pipes or ground rods

General

Catalog Number	2512
Material	Bronze Alloy
UPC	050169025123

Dimensions

Dimensions	2.5 in x 2.25 in x 3.125 in
Height	3.125 in
Length	2.5 in
Weight	0.388 lb
Width	2.25 in



*Representative Image

Conductor Related

Conductor Range	#6 AWG to #10 AWG
-----------------	-------------------

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	25
Minimum Pack Quantity	25

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - UL COC-E195975-1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Intersystem Bonding Bridge](#)
- [Specifications - 2512](#)
- [Terms and Conditions - HCC Terms & Conditions](#)