



1.25 in to 2 in Ground Clamp for 0.5 in Rigid Conduit, Bronze Alloy

By Raco
Catalog # 2522

1.25 in to 2 in Ground Clamp for 0.5 in Rigid Conduit, Bronze Alloy



*Representative Image

Features

- Bronze cast construction assures ground path continuity and provides corrosion resistance
- Additional sizes available

General

Application	For use with grounding wire or conduit to water pipes or ground rods
Material	Bronze Alloy
UPC	050169025222

Dimensions

Dimensions	1.938 in x 1.938 in x 3.5 in
Height	3.5 in
Length	1.938 in
Weight	0.625 lb
Width	1.938 in

Conductor Related

Conductor Range	#6 AWG to #10 AWG
-----------------	-------------------

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	3000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC-E195975-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Sell Sheets - Intersystem Bonding Bridge](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand