



1 in Beam Clamp, 27/32 in Inside Opening, Steel

By Raco
Catalog # 2524

1 in Beam Clamp, 27/32 in Inside Opening, Steel

Features

- Rugged steel/malleable iron construction will last the lifetime of the installation
- Zinc electroplated for corrosion resistance
- Additional sizes available

Application

For use with hangers, bridle rings, and drop rods to support conduit from I-beams

General

Catalog Number	2524
Material	Steel
Max Load Lbs.	60 lb
UPC	050169025246

Dimensions

Dimensions	1.35 in x 1.2 in x 1.35 in
Height	1.35 in



*Representative Image

Length	1.35 in
Trade Size	1 in
Weight	0.24 lb
Width	1.2 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	14400

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Certifications - UL COC - E195968-3](#)
[SDS - HCC SDS](#)
[Specifications - 2524](#)
[Terms and Conditions - HCC Terms & Conditions](#)