



4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in. KO & Twelve TKO's, Raised, FM Bracket

By Raco
Catalog # [254](#)

4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in. KO & Twelve TKO's, Raised, FM Bracket



Features

- Pre-galvanized steel construction
- FM bracket allows the box to be mounted on flat side of the metal or wood stud
- 1/2 in. and 3/4 in. combination TKO knockouts allow for design and installation flexibility
- One 1/2 in. knockout and twelve TKO knockouts
- Combination screw heads provide for faster installation
- 42 cu. in. capacity

General

Bracket Setback	0.375
Bracket Type	FM, for Metal or Wood Studs
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in.; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169002544
Wiring System	Conduit

Dimensions

Actual Depth	2.188 in
Cubic Capacity	42 cu.in
Depth	2.125 in
Height	7.625 in
Raised Ground	Yes
Weight	1.318 lb
Width	5.063 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 2](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-5](#)
[Sales Drawings - 254](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-254-SPEC-EN | REV 6/2024