



3-3/4 in. Square Box, Large capacity, Welded, 3-1/2 in. Deep, Seventeen Knockouts

By Raco
Catalog # 256



*Representative Image

3-3/4 in. Square Box, Large capacity, Welded, 3-1/2 in. Deep, Sixteen 1/2 and 3/4 in. Concentric KO's and One 1/2 in. KO

Features

- Welded steel construction
- 3-3/4 in. square x 3-1/2 in. deep
- 3-3/4 in. opening in wall allows for margin of error when using a 4 in. square cover
- Accepts all 4 in. square covers and mudrings
- Large capacity design accommodates oversized devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with sixteen 1/2-3/4 Concentric KO's and one 1/2 in. KO
- 40.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Yes
Fire Resistance	Yes
Knockouts	1/2 in.; 1/2 - 3/4 in Concentric
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
	Large Capacity
UPC	050169002568
Wiring System	Conduit

Dimensions

Actual Depth	3.5 in
Cubic Capacity	45 cu.in
Depth	3.5 in
Height	3.75 in
Raised Ground	No
Weight	1.204 lb
Width	3.75 in

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1350

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-9](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Sell Sheets - Large Capacity Steel Wall Boxes](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-256-SPEC-EN | REV 6/2024