



4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in. KO & Fifteen TKO's, Raised, 8 in. #12 Stranded Copper Pigtail

By Raco
Catalog # 257F



4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in. KO & Fifteen TKO's, Raised, 8 in. #12 Stranded Copper Pigtail

Features

- Combination screw heads provide for faster installation.
- TKO knockouts allow for design and installation flexibility.
- UBS Support - Welded to box, preset bend points to work with wall thickness 2-1/2 in. to 6 in.
- Welded steel construction
- 4-11/16 in. square x 2-1/8 in. deep
- Supplied with one 1/2 in. and fifteen 1/2 and 3/4 in. TKO knockouts
- Combination Phillips/slotted screw heads
- 8 in. #12 stranded pigtail

General

Bracket Type	No Bracket
Catalog Number	257F
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169500088
Wiring System	Conduit

Dimensions

Actual Depth	2.188 in
Cubic Capacity	42 cu.in
Depth	2.125 in
Height	4.688 in
Raised Ground	Yes
Weight	1.15 lb
Width	4.688 in

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity 20
Pallet Quantity 1080

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 2](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-5](#)
[Sales Drawings - 257F](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-257F-SPEC-EN | REV 6/2024