



4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in. KO & Fifteen TKO's, Raised, 10 in. #12 Stranded Copper Pigtail

By Raco
Catalog # [257SM](#)



4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in. KO & Fifteen TKO's, Raised, 10 in. #12 Stranded Copper Pigtail

Features

- Combination screw heads provide for faster installation
- TKO knockouts allow for design and installation flexibility
- Ideal for surface mount applications
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- 42.0 cu. in. capacity
- Made of pre-galvanized steel

General

Bracket Type	No Bracket
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in.; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169982570
Wiring System	Conduit

Dimensions

Actual Depth	2.188 in
Cubic Capacity	42 cu.in
Depth	2.125 in
Height	4.688 in
Raised Ground	Yes
Weight	1.151 lb
Width	4.688 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1500

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 2](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-5](#)
[Sales Drawings - 257SM](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-257SM-SPEC-EN | REV 6/2024