



4-11/16 in. Square Box, Large Capacity, Welded, 3-1/4 in. Deep, Twelve Knockouts

By Raco
Catalog # 260



4-11/16 in. Square Box, Large Capacity, Welded, 3-1/4 in. Deep, (2) 1/2 in. KO, (4) 1/2 - 3/4 in. TKO, (2) 3/4 - 1 in. TKO, (2) 1 - 1-1/4 in. TKO, (2) 1, 1-1/4, 1-1/2, 2 in. KO

Features

- Large capacity design measures 4-11/16 in. H x 4-11/16 in. W x 3-1/4 in. D
- Accepts standard 4-11/16 in. square device and flat covers
- Ground screws provided
- 4-11/16 in. square x 3-1/4 in. deep
- Welded construction

General

Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Yes
Knockouts	1/2 in.;1/2 - 3/4 in Combination (TKO);3/4 - 1 in Combination (TKO);1-1-1/4 Combination (TKO);1, 1-1/4, 1-1/2, 2 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	<ul style="list-style-type: none">• Box• Large Capacity
UPC	050169002605
Wiring System	Conduit

Dimensions

Actual Depth	3.55 in
Cubic Capacity	66.7 cu.in
Depth	3.25 in
Height	4.69 in
Raised Ground	Yes
Weight	1.57 lb
Width	4.69 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	10
Packaging Type	No Packaging
Pallet Quantity	480

Product Assets

[Brochures - Product Solutions for Electrical Prefabrication](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Sales Drawings - 260](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC_SDS](#)
[Sell Sheets - Large Capacity Box - 66.0 cu. in.](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-260-SPEC-EN | REV 6/2024