



4-11/16 in. Square Box, Large Capacity, Welded, 3-1/4 in. Deep, 12 Knockouts, Raised Ground, H Bracket, Far-Side Box Support

By Raco
Catalog # [260H](#)



4-11/16 in. Square Box, Large Capacity, Welded, 3-1/4 in. Deep, (2) 1/2 in. KO, (4) 1/2 - 3/4 in. TKO, (2) 3/4 - 1 in. TKO, (2) 1 - 1-1/4 in. TKO, (2) 1, 1-1/4, 1-1/2, 2 in. KO, Raised Ground, H Bracket, Far-Side Box Support

Features

- Welded steel construction with "H" bracket which allows for side-by-side mounting on stud and far side box support
- 4-11/16 in. square x 3-1/4 in. deep
- Accepts standard 4-11/16 in. covers
- TKO® Knockouts allow for design and installation flexibility
- Includes knockouts 1/2 in through 2 in.
- Three pre-installed ground screws

Application

RACO® Large capacity boxes are used for audio, video, data and power applications providing ample space for Cat 6A and fiber optic cable bends

General

Bracket Type	H, for Metal or Wood Studs
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO);3/4 - 1 in Combination (TKO);1-1-1/4 Combination (TKO);1, 1-1/4, 1-1/2, 2 in Combination (TKO)
Material	Steel
Type	<ul style="list-style-type: none">• Box• Large Capacity
UPC	050169500507

Dimensions

Actual Depth	4.69 in
Cubic Capacity	66.7 cu.in
Depth	3.25 in
Height	3.25 in
Weight	1.651 lb
Width	4.69 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	10
Pallet Quantity	480

Product Assets

[Brochures - Product Solutions for Electrical Prefabrication](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Sales Drawings - 260H](#)
[SDS - HCC_SDS](#)
[Sell Sheets - Large Capacity Box - 66.0 cu. in.](#)
[Sell Sheets - Large Capacity Box with Stud Mount Bracket](#)
[Sell Sheets - RACO® Life Safety Support Products](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-260H-SPEC-EN | REV 6/2024