



4-11/16 in. x 7-3/4in. Box, Large Capacity, Welded, 3-1/4 in. Deep, 20 Knockouts

By Raco
Catalog # 263



4-11/16 in. x 7-3/4in. Box, Large Capacity, Welded, 3-1/4 in. Deep, (10) 1/2 - 3/4 in. TKO, (4) 3/4 - 1 in. TKO, (4) 1 - 1-1/4 in. TKO, (2) 1, 1-1/4, 1-1/2, 2 in. KO

Features

- Large capacity design measures 4-11/16 in. H x 7-3/4 in. W x 3-1/4 in. D
- Accepts standard 4 in. square device and flat covers or 792, 793, 794 3-gang device covers
- Built-in tabs for spanner bars
- Includes 1/2 in. thru 2 in. knockouts
- Accepts 981 voltage partition (UL Listed)
- Ground screw provided
- 7-3/4 in. wide
- 4-11/16 in. square x 3-1/4 in. deep

General

Bracket Type	No Bracket
Catalog Number	263
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 - 3/4 in Combination (TKO);3/4 - 1 in Combination (TKO);1-1-1/4 Combination (TKO);1, 1-1/4, 1-1/2, 2 in Combination (TKO)
Material	Steel
Number of Gang(s)	3-Gang
Type	Box
	Large Capacity
UPC	050169002636
Wiring System	Conduit

Dimensions

Actual Depth	9.69 in
Cubic Capacity	113.3 cu.in
Depth	3.25 in
Height	3.5 in
Raised Ground	Yes
Weight	2.85 lb
Width	5.5 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	6
Packaging Type	No Packaging
Pallet Quantity	192

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Sales Drawings - 263 Customer Drawing](#)
[SDS - HCC SDS](#)
[Sell Sheets - Large Capacity Outlet Box 113.3 cu. in.](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-263-SPEC-EN | REV 6/2024