



## 4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in., Four 3/4 in., Four 1 in. KO's and 3 TKO's, Raised Ground

By Raco  
Catalog # 265



4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in., Four 3/4 in., Four 1 in. KO's and 3 TKO's, Raised

### Features

- Combination screw heads provide for faster installation
- TKO knockouts allow for design and installation flexibility

### General

Bracket Type	No Bracket
Drawn or Welded	Welded
EU RoHS Indicator	Yes
Knockouts	1/2 in.;3/4 in.;1 in.;1/2 - 3/4 in Combination (TKO)
Material	Steel
Type	Box
UPC	050169902653
Wiring System	Conduit

### Dimensions

Actual Depth	2.188 in
Cubic Capacity	42 cu.in
Depth	2.125 in
Height	4.688 in
Raised Ground	Yes
Weight	1.108 lb
Width	4.688 in

### Certifications And Compliance

Certified Listed                      UL Listed

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1500

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Certifications - UL COC - E195978-5](#)  
[Sales Drawings - 265](#)  
[Sales Drawings - RACO-welded-steel-box-infographic](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-265-SPEC-EN | REV 6/2024