



1/2 in. 90 Degree Rigid/IMC Handy EII Threaded Coupling

By Raco
Catalog # [2652](#)



1/2 in. 90 Degree Rigid/IMC Handy EII Threaded Coupling

*Representative Image

Features

- Gasket and cover included
- Additional sizes available

General

| | |
|-------------------|----------------------|
| Conduit Type | Rigid/IMC |
| EU RoHS Indicator | Contact Manufacturer |
| Fitting Type | Couplings |
| Material | Die Cast Zinc |
| UPC | 050169026526 |

Dimensions

| | |
|------------|--------------------------|
| Dimensions | 1 in x 1.75 in x 1.75 in |
| Height | 1.75 in |
| Length | 1 in |
| Trade Size | 1/2 in |
| Weight | 0.269 lb |
| Width | 1.75 in |

Certifications And Compliance

| | |
|----------------------|---|
| Certified Listed | <ul style="list-style-type: none">• UL Listed• CSA Certified |
| Industry Standard(s) | UL 514B |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 100 |
| Minimum Pack Quantity | 10 |
| Pallet Quantity | 4000 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2652-SPEC-EN | REV 6/2024