



3/4 in. 90 Degree Rigid/IMC Handy EII Threaded Coupling

By Raco
Catalog # [2653](#)

3/4 in. 90 Degree Rigid/IMC Handy EII Threaded Coupling

Features

- Gasket and cover included
- Additional sizes available

General

Catalog Number	2653
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Couplings
Material	Die Cast Zinc
UPC	050169026533

Dimensions

Dimensions	1.25 in x 1.5 in x 2.5 in
Height	2.5 in
Length	1.25 in
Trade Size	3/4 in
Weight	0.3 lb
Width	1.5 in



*Representative Image

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	50
Minimum Pack Quantity	5
Pallet Quantity	2000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Specifications - 2653](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand