



1-1/4 in. 90 Degree Rigid/IMC Handy EII Threaded Coupling

By Raco
Catalog # 2655



1-1/4 in. 90 Degree Rigid/IMC Handy EII Threaded Coupling

*Representative Image

Features

- Gasket and cover included
- Additional sizes available

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Yes
Fitting Type	Couplings
Material	Die Cast Zinc
UPC	050169026557

Dimensions

Dimensions	4.57 in x 1.93 in x 2.55 in
Height	2.55 in
Length	4.57 in
Trade Size	1-1/4 in
Weight	0.915 lb
Width	1.93 in

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	20
Minimum Pack Quantity	20
Pallet Quantity	2200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2655-SPEC-EN | REV 6/2024