



1/2 in. 90 Degree Rigid/IMC Handy EII Threaded Connector

By Raco
Catalog # [2662](#)

1/2 in. 90 Degree Rigid/IMC Handy EII Threaded Connector

Features

- Gasket and cover included
- Additional sizes available

General

Catalog Number	2662
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Material	Die Cast Zinc
UPC	050169026625

Dimensions

Dimensions	2.4 in x 1.027 in x 1.49 in
Height	1.49 in
Length	2.4 in
Trade Size	1/2 in
Weight	0.31 lb
Width	1.027 in



*Representative Image

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	100
Minimum Pack Quantity	10
Pallet Quantity	4000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Specifications - 2662](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand