



1-1/4 in. 90 Degree Flex Squeeze Connector, Uninsulated

By Raco
Catalog # 2695

1-1/4 in. 90 Degree Flex Squeeze Connector, Uninsulated



*Representative Image

Features

- Rugged metallic construction ensures mechanical protection for the raceway
- Additional sizes available

General

Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Material	Die Cast Zinc
UPC	050169026953

Dimensions

Dimensions	3.94 in x 2.859 in x 3 in
Height	3 in
Length	3.94 in
Trade Size	1-1/4 in
Weight	0.501 lb
Width	2.859 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	40
Minimum Pack Quantity	10
Pallet Quantity	1600

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand