



## 2 in. 90 Degree Flex Squeeze Connector, Uninsulated

By Raco  
Catalog # 2698



2 in. 90 Degree Flex Squeeze Connector, Uninsulated

### Features

- Rugged metallic construction ensures mechanical protection for the raceway
- Additional sizes available

### General

Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Material	Die Cast Zinc
UPC	050169026984

### Dimensions

Dimensions	6.25 in x 4 in x 4 in
Height	4 in
Length	6.25 in
Trade Size	2 in
Weight	1.23 lb
Width	4 in

### Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	600

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand