



3/4 in. 90 Degree EMT Handy EII Connector

By Raco
Catalog # 2763



3/4 in. 90 Degree EMT Handy EII Connector

*Representative Image

Features

- Rugged metallic construction ensures mechanical protection
- 90° EII
- UL Listed, CSA
- Available in trade sizes of 1/2 in or 3/4 in.
- Cover included

General

Conduit Type	EMT
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Material	Die Cast Zinc
UPC	050169027639

Dimensions

Dimensions	2.77 in x 1.36 in x 1.475 in
Height	1.475 in
Length	2.77 in
Trade Size	3/4 in
Weight	0.45 lb
Width	1.36 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified

Logistics

Carton Quantity	50
Minimum Pack Quantity	5
Pallet Quantity	2000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand