




## Concrete Ring, Welded, 4 in. Deep, Double Row 3/4 & 1 in. KO's

By Raco  
Catalog # 279

Concrete Ring, Welded, 4 in. Deep, Double Row 3/4 & 1 in. KO's



### Features

- Flat sides provide excellent contact for locknuts
- External ears are used to nail the ring to the wood form
- Top cover is removable for before-pour work
- Ears on inside of box are for fixtures
- Waxed fixture ears prevent concrete from interfering with the threads
- A variety of covers are available
- Cover plate must be ordered separately with all RACO® concrete rings
- Back plate with 3/8 in. threaded fixture stud included (Raco 891)
- Slots provided for Raco 918 bars (sold separately)
- 43.0 cu. in. capacity
- Not designed for ceiling fan support, the maximum support load for a static fixture is 50 lbs

### General

Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Knockouts	3/4 in;1 in
Material	Steel
Type	Concrete Ring
UPC	050169002797
Wiring System	Conduit

### Dimensions

Cubic Capacity	49.3 cu.in
Depth	4 in
Fixture Lbs.	50 lb
Height	4 in
Weight	1.04 lb
Width	4 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	20
Packaging Type	No Packaging
Pallet Quantity	1000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-18](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Certifications - UL COC - E195978- 3](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-279-SPEC-EN | REV 6/2024