



Hung Ceiling Box, 3-1/2 in. Deep, Includes 890 Cover, Double Row KO's, Eight 1/2 in. & Eight 3/4 in. KO

By Raco
Catalog # 280



Hung Ceiling Box, 3-1/2 in. Deep, Includes 890 Cover, Double Row KO's, Eight 1/2 in. & Eight 3/4 in. KO

Features

- Flat sides provide excellent contact for locknuts
- External ears are used to nail the ring to the wood form
- Top cover is removable for before-pour work
- Ears on inside of box are for fixtures
- Waxed fixture ears prevent concrete from interfering with the threads
- A variety of covers are available
- Cover plate must be ordered separately with all RACO® concrete rings
- Used in high-rise construction
- 49.3 cu. in. capacity
- Maximum support load for ceiling fans is 35 lbs. and for a static fixture is 75 lbs

General

Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in.;3/4 in
Material	Steel
Type	Ceiling Box
UPC	050169002803
Wiring System	Conduit

Dimensions

Actual Depth	4.875 in
Cubic Capacity	43 cu.in
Depth	3.5 in
Height	4 in
Weight	1.257 lb
Width	5 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	20
Packaging Type	No Packaging
Pallet Quantity	1100

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-280-SPEC-EN | REV 6/2024