



2-1/2 in. EMT Compression Connector, Uninsulated

By Raco
Catalog # 2840

2-1/2 in. EMT Compression Connector, Uninsulated



*Representative Image

Features

- Rugged metallic construction ensures mechanical protection
- Noninsulated
- Oversized hex compression nuts assure easy wrench installation
- UL Listed, CSA
- Available in trade sizes of 1/2 in. through 4 in.

General

Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Die Cast Zinc
UPC	050169028407

Dimensions

Dimensions	2.703 in x 3.156 in x 3.156 in
Height	3.156 in
Length	2.703 in
Trade Size	2-1/2 in
Weight	1.042 lb
Width	3.156 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified

Logistics

Carton Quantity	12
Minimum Pack Quantity	12
Pallet Quantity	1320

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195970- 1](#)
[Certifications - UL COC - E195970 - 3](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-2840-SPEC-EN | REV 6/2024