



Nonmetallic 1 in. KO Sheathed Cable Connector

By Raco
Catalog # 2864

Nonmetallic 1 in. KO Sheathed Cable Connector



*Representative Image

Features

- Rugged metallic construction will last the life of the installation
- Additional size available

General

Accessory Type	Fitting
Conduit Type	Service Entrance
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Material	Die Cast Zinc
UPC	050169028643

Dimensions

Dimensions	1.11 in x 1.94 in x 1.375 in
Height	1.375 in
Length	1.11 in
Trade Size	1 in
Weight	0.162 lb
Width	1.94 in

Conductor Related

Cable Size	4 #12, 3 #12, 4 #10, 3 #10, 3 #8, 2 #8, 2 #6, 2 #4
------------	--

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	250
Minimum Pack Quantity	25
Pallet Quantity	12000

Product Assets

[Brochures - HCC Products for Solar](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195972-1](#)
[Product Logo - NMSC](#)
[Product Logo - SE CABLE](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2864-SPEC-EN | REV 6/2024