



3-1/2 in. Round Ceiling Pan, Drawn, 3/4 in. Deep, One 1/2 in. KO and NMSC Clamps

By Raco
Catalog # 287

3-1/2 in. Round Ceiling Pan, Drawn, 3/4 in. Deep, One 1/2 in. KO
and NMSC Clamps

Features

- Steel construction
- NMSC clamps for an easy connection
- Houses the wiring for a ceiling fixture
- Supplied with one 1/2 in. knockout
- Combination screw heads provide for faster installation

General

Catalog Number	287
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	3.5 in
Type	Ceiling Pan
UPC	050169002872
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	0.75 in
Cubic Capacity	5 cu.in
Depth	0.75 in
Fixture Lbs.	50 lb
Height	3.375 in



Raised Ground	No
Weight	0.34 lb
Width	3.375 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed
Description SPEC - Certification	Canada 1,324,360; Mexico 166,125.

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	6300

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 287 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 287](#)
[Terms and Conditions - HCC Terms & Conditions](#)