



1-1/4 in. EMT Raintight Compression Connector, Uninsulated

By Raco
Catalog # 2905RT



1-1/4 in. EMT Raintight Compression Connector, Uninsulated

Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Marked with "Wet Location" for easy inspection
- cULus
- Available in trade sizes of 1/2 in. through 4 in.
- Installed knockout seal

General

Catalog Number	2905RT
Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel
UPC	050169290590

Dimensions

Dimensions	2.076 in x 1.91 in x 2.04 in
Height	2.04 in
Length	2.076 in

Trade Size	1-1/4 in
Weight	0.369 lb
Width	1.91 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	20
Minimum Pack Quantity	20
Pallet Quantity	4160

Product Assets

[Brochures - HCC Products for Solar](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Certifications - UL COC - E195970 - 2](#)
[Product Logo - Conduit](#)
[Sales Drawings - 2905RT-CHINA Customer Drawing](#)
[SDS - HCC SDS](#)
[Sell Sheets - Raintight Steel EMT Compression Fittings](#)
[Specifications - 2905RT](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand