



1/2 in. EMT Raintight Compression Connector, Insulated

By Raco
Catalog # 2912RT

1/2 in. EMT Raintight Compression Connector, Insulated



*Representative Image

Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insulated
- Marked with "Wet Location" for easy inspection
- cULus
- Available in trade sizes of 1/2 in. through 4 in.
- Installed knockout seal

General

Catalog Number	2912RT
Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel
UPC	050169291290

Dimensions

Dimensions	1.621 in x 1.05 in x 1.12 in
Height	1.12 in

Length	1.621 in
Trade Size	1/2 in
Weight	0.1 lb
Width	1.05 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	250
Pallet Quantity	15000

Product Assets

- [Brochures - HCC Products for Solar](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - UL COC - E195970 - 2](#)
- [Product Logo - Conduit](#)
- [Sales Drawings - 2912RT-CHINA Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Raintight Steel EMT Compression Fittings](#)
- [Terms and Conditions - HCC Terms & Conditions](#)