



# 3/4 in. EMT Raintight Compression Connector, Insulated

By Raco  
Catalog # 2913RT

3/4 in. EMT Raintight Compression Connector, Insulated

## Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insulated
- Marked with "Wet Location" for easy inspection
- cULus
- Available in trade sizes of 1/2 in. through 4 in.
- Installed knockout seal

## General

Catalog Number	2913RT
Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel
UPC	050169291399

## Dimensions

Dimensions	1.762 in x 1.255 in x 1.35 in
Height	1.35 in
Length	1.762 in



\*Representative Image

Trade Size	3/4 in
Weight	0.145 lb
Width	1.255 in

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	125
Minimum Pack Quantity	25
Pallet Quantity	10000

## Product Assets

[Brochures - HCC Products for Solar](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Certifications - UL COC - E195970 - 2](#)  
[Product Logo - Conduit](#)  
[Sales Drawings - 2913RT-CHINA Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - Raintight Steel EMT Compression Fittings](#)  
[Specifications - 2913RT](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand