



3-1/2 in. Round Ceiling Pan, Drawn, 1/2 in. Deep, One 1/2 in. KO and NMSC Clamps

By Raco
Catalog # 292



3-1/2 in. Round Ceiling Pan, Drawn, 1/2 in. Deep, One 1/2 in. KO
and NMSC Clamps

Features

- Rated for 50 lb. fixture support
- Combination screw heads provide for faster installation
- L clamps provided for Nonmetallic Sheathed Cable (NMSC)
- Supplied with 1/2 in. knockout
- 6.0 cu. in. capacity
- Do not use to support ceiling fans

General

Catalog Number	292
Ceiling Fan Rated	No
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	3.5 in
Type	Ceiling Pan
UPC	050169902929
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	0.563 in
Cubic Capacity	4 cu.in
Depth	0.5 in
Fixture Lbs.	50 lb
Height	3.375 in
Raised Ground	No

Weight	0.296 lb
Width	3.375 in

Certifications And Compliance

Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2024)
Buy American Compliant Certified Listed	Yes <ul style="list-style-type: none">• UL Listed•
Description SPEC - Certification	Canada 1,324,360; Mexico 166,125.

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	7200

Product Assets

[Catalogs - Steel Boxes, Covers and Accessories](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 292 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 292](#)
[Terms and Conditions - HCC Terms & Conditions](#)