



# 1-1/4 in. EMT Raintight Compression Coupling

By Raco  
Catalog # [2925RT](#)



1-1/4 in. EMT Raintight Compression Coupling

\*Representative Image

## Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Marked with "Wet Location" for easy inspection
- cULus
- Available in trade sizes of 1/2 in. through 4 in.

## General

Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Couplings
Material	Steel
UPC	050169292594

## Dimensions

Dimensions	2.955 in x 1.91 in x 2.04 in
Height	2.04 in
Length	2.955 in
Trade Size	1-1/4 in
Weight	0.454 lb
Width	1.91 in

## Certifications And Compliance

Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	20
Minimum Pack Quantity	20
Pallet Quantity	4400

## Product Assets

[Brochures - HCC Products for Solar](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195970 - 2](#)  
[Product Logo - Conduit](#)  
[Sales Drawings - 2922RT](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-2925RT-SPEC-EN | REV 6/2024