



## 4 in. Round Ceiling Rated Box, 2-1/8 in. Deep, Three 1/2 KO's, for New and Old Work

By Raco  
Catalog # 294-1



4 in. Round Ceiling Rated Box, 2-1/8 in. Deep, Three 1/2 KO's, for New and Old Work

### Features

- No protruding ground screw or fan mounting screws allows easy installation
- Metal protection plate eliminates debris or damage to wiring
- Setback tab allows for easy installation of different wall thickness
- New work applications rated at 150 lbs. Old work applications rated at 70 lbs
- Supplied with three 1/2 in. knockouts
- #10-32, 1 in. long ceiling fan screws provided and provision for #8-32 fixture mounting screw
- Easy to follow instructions and mounting hardware included

### General

Bracket Type	Old or New Work
Catalog Number	294-1
Ceiling Fan Rated	Yes
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Ceiling;Light
Knockouts	1/2 in
Material	Steel
Old Work or New Work	New Work
	Old Work
Size	4 in
Type	Box
UPC	050169902943

### Dimensions

Ceiling Fan Lbs.	70 lb
Cubic Capacity	22.3 cu.in
Depth	2.125 in
Fixture Lbs.	70-150 lb
Height	4.25 in
Raised Ground	Yes
Weight	1.28 lb
Width	4.06 in

### Certifications And Compliance

Certified Listed                      UL Listed

### Logistics

Carton Quantity	10
Packaging Type	Box
Pallet Quantity	960

### Product Assets

- [3D Models - 294-NW3D](#)
- [3D Models - 294 OW3D](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Installation Manuals - Ceiling Fan Installation Instructions](#)
- [Installation Manuals - Installation Instructions for 294, 294-1 & 294XL](#)
- [Sales Drawings - 294](#)
- [Sales Drawings - RACO-drawn-steel-box-infographic](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - RACO® Ceiling Fan Boxes](#)
- [Sell Sheets - 4 in. Round, 2-1/8 in. Deep, Bracketed Ceiling Box](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: 294 Ceiling Fan Box](#)
- [Video - RACO: Choosing the Correct Ceiling Fan Box](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-2941-SPEC-EN | REV 6/2024