



# 4 in. EMT Raintight Compression Connector, Uninsulated

By Raco  
Catalog # 2946RT



4 in. EMT Raintight Compression Connector, Uninsulated

## Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Marked with "Wet Location" for easy inspection
- cULus
- Available in trade sizes of 1/2 in. through 4 in.
- Installed knockout seal

## General

Catalog Number	2946RT
Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel
UPC	050169501030

## Dimensions

Dimensions	4.021 in x 5.07 in x 5.3 in
Height	5.3 in
Length	4.021 in

Trade Size	4 in
Weight	2.281 lb
Width	5.07 in

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	343

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Certifications - UL COC - E195970 - 2](#)
- [Product Logo - Conduit](#)
- [Sales Drawings - 2946RT-CHINA Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Raintight Steel EMT Compression Fittings](#)
- [Specifications - 2946RT](#)
- [Terms and Conditions - HCC Terms & Conditions](#)