



4 in. Round Ceiling Rated Fan Pan, 1/2 in. Depth, Five 1/2 in. KO's

By RACO
Catalog # 295

4 in. Round Ceiling Rated Fan Pan, 1/2 in. Depth, Five 1/2 in. KO's



Features

- Steel construction
- No protruding ground screw or fan mounting screws allows easy installation
- Metal protection plate eliminates debris or damage to wiring
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Maximum support load for ceiling fans 70 lbs. and 150 lbs. for static light fixtures
- Supplied with five 1/2 in. knockouts
- Easy to follow instructions and mounting hardware included
- 6.0 cu. in. capacity

Specifications

Certified Listed	UL Listed
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Configuration

Knockouts	1/2 in
-----------	--------

Dimensions

Cubic Capacity	6.0 cu.in
Fixture Lbs.	150 lb.
Depth	0.5 in
Size	4 in
Actual Depth	1.13 in

Ceiling Fan Lbs.	70 lb.
Raised Ground	Yes
Width	4.38 in
Weight	0.64 lb.
Height	4.38 in

General

Series	THE INSIDER®
Fixture Type	<ul style="list-style-type: none"> • Ceiling • Light
Ceiling Fan Rated	Yes
Type	Ceiling Pan
Material	Steel
Drawn or Welded	Drawn
UPC	050169002957

Logistics

Packaging Type	No Packaging
Carton Quantity	10
Pallet Quantity	2560

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)