



2-1/2 in. EMT Raintight Compression Coupling

By Raco
Catalog # 2950RT

2-1/2 in. EMT Raintight Compression Coupling



*Representative Image

Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Marked with "Wet Location" for easy inspection
- cULus
- Available in trade sizes of 1/2 in. through 4 in.

General

Catalog Number	2950RT
Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Couplings
Material	Steel
UPC	050169501085

Dimensions

Dimensions	4.749 in x 3.44 in x 3.62 in
Height	3.62 in
Length	4.749 in

Trade Size	2-1/2 in
Weight	1.769 lb
Width	3.44 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	576

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195970 - 2](#)
[Product Logo - Conduit](#)
[Sales Drawings - 2950RT-CHINA Customer Drawing](#)
[SDS - HCC SDS](#)
[Sell Sheets - Raintight Steel EMT Compression Fittings](#)
[Terms and Conditions - HCC Terms & Conditions](#)